

Base fabric:	Polyaramid woven fabric
Outside coating:	Butyl rubber with outer Viton rubber layer
Inside coating:	Multi-layer barrier film
Weight, nominal	695 g/m ²
Colour (outside / inside)	Red / White

Physical performance (EN 943-1:2015, EN 943-2:2002, EN 14325:2004)			
	Test method	Result	Class
Abrasion	EN 530	> 2000 cycles	6 of 6
Flex cracking	ISO 7854:B	> 15 000 cycles	4 of 6
Flex cracking @ -30 °C	ISO 7854:B	> 2000 cycles	5 of 6
Tear resistance	EN ISO 9073-4	> 40 N	3 of 6
Tensile strength	EN ISO 13934-1	> 1000 N	6 of 6
Puncture resistance	EN 863	> 50 N	3 of 6
Resistance to flame	EN 13274-4, meth 3	5 Sec	3 of 3
Seam strength	ISO 5082	> 500 N	6 of 6
Additional tests			
Limited flame spread index	EN ISO 14116	Pass	3 of 3
Antistatic properties	EN 1149-5	Pass	n.a.

Barrier performance – Chemical permeation (EN 943-2:2002, EN 14325:2004)					
Chemical	BT (min)	Class	Chemical	BT (min)	Class
Acetone	> 480	6	Heptane	> 480	6
Acetonitrile	> 480	6	Hexane	> 480	6
Anhydrous Ammonia (gas)	> 480	6	Hydrogen chloride (gas)	> 480	6
Carbon disulphide	> 480	6	Methanol	> 480	6
Chlorine (gas)	> 480	6	Sodium hydroxide 40 %	> 480	6
Dichloromethane	> 480	6	Sulphuric acid 96 %	> 480	6
Diethyl amine	> 480	6	Tetrahydrofuran	> 480	6
Ethyl acetate	> 480	6	Toluene	> 480	6

Tests performed according to EN 374-3 or ISO 6529, breakthrough criterion 1 µg/cm²/min, test duration 8 hours.

NOTE: For up to date chemical data, please visit our online chemical database at <http://protective.ansell.com>

Barrier performance – Infective agent penetration (EN 14126:2003)			
	Test method	Result	Class
Resistance to penetration by contaminated blood and body fluids	ISO 16603	No penetration	6 of 6
Resistance to penetration by blood-borne pathogens	ISO 16604	No penetration	6 of 6
Resistance to wet microbial penetration	EN ISO 22610	No penetration	6 of 6
Resistance to biologically contaminated liquid aerosol penetration	ISO DIS 22611	No penetration	3 of 3
Resistance to dry microbial penetration	ISO 22612	No penetration	3 of 3