



TRELLCHEM SPLASH 600



TRELLCHEM SPLASH 900



TRELLCHEM SPLASH 1000



TRELLCHEM SPLASH 1000S



TRELLCHEM SPLASH 2000

CERTIFICATES & APPROVALS	EN 14605 (type 4 spray tight)	EN 14605 (type 3 liquid tight) ATEX (Zone 1 & 2/Group II A & II B)	EN 14605 (type 3 liquid tight)	EN 14605 (type 4 spray tight)	EN 14605 (type 3 liquid tight)
DESIGN	Basic overall with hood.	Non-encapsulating with face seal. BA worn outside the suit.	Two-piece encapsulating. Jacket with hump and large visor. BA worn inside the suit.	Two-piece "encapsulating". Jacket with hump, face seal and front window. BA worn inside the suit.	Encapsulating design (with hump). BA worn inside the suit.
AREA OF USE	Industry (minimal risk), Shipping	Emergency back-up, Industry, Shipping	Initial on-site response	Initial on-site response.	Industry, Fire & Rescue, Shipping
GARMENT MATERIAL	<ul style="list-style-type: none"> Strong and flexible polyamide fabric, double coated with PVC "Antistatic" according to EN 1149-5 Option: Many different PVC materials & Viton®/butyl rubber material 	<ul style="list-style-type: none"> Polyamide fabric, single coated with PVC "Antistatic" according to EN 1149-5 Option: Double coated PVC fabric (orange or green) 	<ul style="list-style-type: none"> Polyamide fabric, double coated with flame retardant PVC "Antistatic" according to EN 1149-5 	<ul style="list-style-type: none"> Polyamide fabric, double coated with flame retardant PVC "Antistatic" according to EN 1149-5 	<ul style="list-style-type: none"> Polyamide fabric, single coated with PVC "Antistatic" according to EN 1149-5 Option: Double coated PVC fabric (orange or green)
COLOUR	Bright red (green option)	Bright yellow	Yellow with orange details	Yellow with orange details	Bright yellow
GLOVES	<ul style="list-style-type: none"> Open sleeves with Velcro® Option: Trellchem® Bayonet glove ring system with attached gloves 	<ul style="list-style-type: none"> Butyl rubber gloves (standard) Trellchem® Bayonet glove ring system Optional gloves: Chloroprene rubber, PVC or Viton®/butyl rubber 	<ul style="list-style-type: none"> Butyl rubber gloves (standard) Trellchem® Bayonet glove ring system Optional gloves: Chloroprene rubber, PVC or Viton®/butyl rubber 	<ul style="list-style-type: none"> Butyl rubber gloves (standard) Trellchem® Bayonet glove ring system Optional gloves: Chloroprene rubber, PVC or Viton®/butyl rubber 	<ul style="list-style-type: none"> Butyl rubber gloves (standard) Trellchem® Bayonet glove ring system Optional gloves: Chloroprene rubber, PVC or Viton®/butyl rubber
FOOTWEAR	Different style open legs / Attached PVC safety boots / Socks	Open legs / Attached PVC safety boots / Socks	Open legs - boots not included.	Open legs - boots not included.	Open legs / Attached PVC safety boots / Socks
ZIPPER	<ul style="list-style-type: none"> Nylon zipper Option: Watertight PVC zipper Protected by double splash guard (flap) 	<ul style="list-style-type: none"> Long watertight PVC zipper placed on the back, across the shoulders Protected by single splash guard (flap) 	<ul style="list-style-type: none"> Nylon zippers on lower part of jacket and legs for easy donning 	<ul style="list-style-type: none"> Nylon zippers on lower part of jacket and legs for easy donning 	<ul style="list-style-type: none"> Long watertight PVC zipper with closing downwards Placed on the front left-hand side to facilitate donning and doffing Protected by single splash guard (flap)
FEATURES	<ul style="list-style-type: none"> Hood with drawstring and chin flap Hood fits under safety helmet Optional: With stand-up collar. 	<ul style="list-style-type: none"> Anatomically designed face seal Reinforced knees and elbows For use with SCBA or filter mask 	<ul style="list-style-type: none"> Extra large 1 mm flexible PVC visor High waist trousers fitted with suspenders Extremely quick and easy dressing For use with SCBA 	<ul style="list-style-type: none"> Elastic mask seal for tight fit around/outside mask visor Front window on jacket to enable reading of manometer High waist trousers fitted with suspenders For use with SCBA 	<ul style="list-style-type: none"> Large 1 mm flexible PVC visor Reinforced knees and elbows For use with SCBA