



THE WORLDWIDE
DIVING STANDARD

VIKING™ HOODS

VIKING™ NAUTIC NEOPRENE HOOD

Made from 5mm double lined neoprene, and fitted with a 4mm smoothskin face seal which forms a seal with a full face mask. Seams are glued and stitched on the outside. Available with or without reflective VIKING™ logo. A latex neck seal is mounted to the suit underneath the hood.



VIKING™ Nautic neoprene hood.

HOOD SIZE	HEAD SIZE	SUIT SIZE (Unless customer specifies differently)
Small (SML)	55/56 cm	00/SML; 00/SML Wide; 00/SML Dwide
Medium (MED)	57/58 cm	01/MED; 01/MED Wide; 01/MED Dwide
Large (LGE)	59/60 cm	02/LGE; 02/LGE Wide; 02/LGE Dwide
X-Large (EXL)	61/61.5 cm	03/EXL; 03/EXL Wide; 03/EXL Dwide; all sizes above

VIKING™ SMOOTHSKIN NEOPRENE HOOD

Made from 6 mm smoothskin neoprene. Fitted with a 3 mm smoothskin face seal, which forms a seal with a full face mask. Seams are glued, stitched and taped inside. Easier to clean than a nylon hood, and therefore more suited to diving in light contaminants. A latex neck seal is mounted to the suit underneath the hood.



VIKING™ Smoothskin neoprene hood.

HOOD SIZE	HEAD SIZE	SUIT SIZE (Unless customer specifies differently)
Small (SML)	55/56 cm	00/SML; 00/SML Wide; 00/SML Dwide
Medium (MED)	57/58 cm	01/MED; 01/MED Wide; 01/MED Dwide
Large (LGE)	59/60 cm	02/LGE; 02/LGE Wide; 02/LGE Dwide
X-Large (EXL)	61/61.5 cm	03/EXL; 03/EXL Wide; 03/EXL Dwide; all sizes above

VIKING™ SEMI DRY HOOD (NOT ATTACHED TO THE SUIT)

Made from 5 mm neoprene double lined material. Fitted with a 4 mm smoothskin face seal which forms a nice seal with a full face mask. Double glued seams, which are stitched on the outside. Fitted with a VIKING™ logo (non-logo version also available). Velcro adjustable neck area for comfort and ease of donning and doffing.



VIKING™ Semi Dry hood.

HOOD SIZE	HEAD SIZE	SUIT SIZE
Small (SML)	55/56 cm	N/A
Medium (MED)	57/58 cm	N/A
Large (LGE)	59/60 cm	N/A
X-Large (EXL)	61/62 cm	N/A

NOTE: Given the stretch nature of these hoods, all sizes are approximate and issued as a guideline only.



THE WORLDWIDE
DIVING STANDARD

VIKING™ HOODS



VIKING™ Magnum rubber hood.

VIKING™ MAGNUM RUBBER HOOD

Functions just like a normal hood whereby it has a latex face seal, and a latex neck seal attached directly to the suit. The material is extremely puncture and abrasion resistant, just like the suit material. Ideal for contaminated water diving. Velcro adjustable strap at the back of the hood for fitment of the face seal. **MUST** be used with a hood liner for thermal insulation, and to protect the ears.

Available in two versions:

- Magnum Flex made from stretchy PROTECH material
- Magnum HDS for fitting to HDS suits

HOOD SIZE	HEAD SIZE	SUIT SIZE (Unless customer specifies differently)
Medium (MED)	58/59 cm	00/SML; 00/SML Wide; 00/SML Dwide; 01/MED; 01/MED Wide; 01/MED Dwide
Large (LGE)	60/61 cm	02/LGE; 02/LGE Wide; 02/LGE Dwide
X-Large (EXL)	62/63 cm	03/EXL; 03/EXL Wide; 03/EXL Dwide; all sizes above



VIKING™ Surveyor latex hood.

VIKING™ SURVEYOR LATEX HOOD

Latex hood, permanently attached to the suit. Provides a basic level of protection against biological and light contaminants. A latex neck seal is attached to the suit underneath the hood. **MUST** be used with a thermal liner to protect the ears.

HOOD SIZE	HEAD SIZE	SUIT SIZE
Standard	57/60 cm	All suits unless customer specifies SML hood
Small (SML)	52/56 cm	On request

NOTE: Given the stretch nature of these hoods, all sizes are approximate and issued as a guideline only.

Ansell Protective Solutions AB

Arenagatan 8B
215 33 Malmö, Sweden
Tel: +46 10 205 1800
order.protective@ansell.com
<http://protective.ansell.com>

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates.
© 2019 Ansell Limited. All Rights Reserved.

