



THE WORLDWIDE
DIVING STANDARD

VIKING™ PROTECH



VIKING™ PROTECH with Surveyor latex hood.

Flexible drysuit designed for maximum comfort in a wide range of applications, particularly suited to military use. Rear entry design. Vulcanised seams allow for peace of mind when diving under all situations.

- Internal stitched and taped seams
- External vulcanised seams
- Easy to clean exterior when contaminated
- Easy to repair in the field to minimise downtime
- Extremely flexible and comfortable

DESIGN

Rear entry. Available in two models; VIKING™ PROTECH and VIKING™ PROTECH BE NAVY.

SUIT MATERIAL

Blend of natural and synthetic rubbers (NR/EPDM), on a stretch polyamide/elastane lining.

Total material weight: 1250 g/m² ± 100 g/m².

SEAMS

Internal: Stitched together with an elastic tape for security.

External: Vulcanised with a 25 mm rubber tape.

Vulcanisation is a chemical bonding process, ensuring watertight seams.

REINFORCEMENTS

Additional layers of anti-slip textured rubber are applied to areas at risk of wear. The shoulders, zipper and waistband are reinforced. The trouser rear reinforcement extends around the thigh and across to the front of the legs, and down to the boots.


COLOUR

All black. Military version has black logos.



THE WORLDWIDE
DIVING STANDARD

VIKING™ PROTECH



Internal stitched seam

ZIPPER

PROTECH: Medium Duty (MD) non-magnetic; 90 cm long.

PROTECH BE NAVY: Heavy Duty (HD) non-magnetic; 90 cm long.
The zipper is placed across the shoulders.

VALVES

Standard configuration, mounted on rubber backing discs:

- Push protected inlet valve, positioned centrally on the chest
 - Hose: 80 cm long; CEJN fitting
 - Low profile adjustable exhaust valve, on the upper left arm
- VIKING™ PROTECH BE NAVY is fitted with non-magnetic inlet and exhaust valves.

NECK SEAL

Fitted with a Surveyor latex neck seal as standard.

Option: VIKING™ Quick Neck system, which allows for quick changing of broken seals.

HOOD OPTIONS

May be fitted with a wide range of hood options as follows:
Surveyor latex hood + thermal inner hood, Nautic neoprene hood with smooth face seal or Smoothskin hood.

CUFFS

Latex PRO cuffs are the standard fitment.

Options: A rubber cuff ring system or the VIKING™ Bayonet Ring System. Both systems make the fitment of rubber gloves possible.

FOOTWEAR

Rubber coated 5 mm neoprene boots. The boots feature a non-slip outsole and a heel fin retainer. Alternative options are available.

SIZE RANGE

- Regular: 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL, 05/XXXL
- Wide: 01/MED, 02/LGE, 03/EXL, 04/XXL
- Double Wide: 01/MED, 02/LGE, 03/EXL, 04/XXL

See the VIKING™ size chart for detailed size measurements along with boot sizing.

INCLUDED WITH EACH DELIVERY

Each suit comes supplied with suspenders, carry bag, user manual, repair kit and zip care materials.

CERTIFICATION & APPROVALS

- EN 14225-2:2005
- BIO micro-organism approval
- HZ chemical approval (only VIKING™ PROTECH BE Navy)

Ansell Protective Solutions AB
Johan Kocksgatan 10, SE-231 81 Trelleborg, Sweden
Tel: +46 10 205 1800, Fax: +46 10 205 1840
<http://protective.ansell.com> | order.protective@ansell.com

® & ™ are trademarks owned by Ansell Limited or one of its affiliates.
© 2017 Ansell Limited. All Rights Reserved.

Ansell