



THE WORLDWIDE  
DIVING STANDARD

## VIKING™ PRO



VIKING™ PRO with Surveyor latex neck seal  
(inset shows black suit with Surveyor latex  
hood).

The VIKING™ PRO is Ansell's biggest selling dry suit worldwide. Designed for flexibility and comfort in a wide range of applications. Vulcanised seams allow for peace of mind when diving under all situations.

- Internal stitched and taped seams
- External vulcanised seams
- Easy to clean exterior when contaminated
- Easy to repair in the field to minimise downtime
- Flexible and comfortable

### DESIGN

Rear entry.

### SUIT MATERIAL

Blend of natural and synthetic rubbers (NR/EPDM), on a 2-way stretch knitted polyester lining.

**Total material weight:** 1050 g/m<sup>2</sup> ± 100 g/m<sup>2</sup>.

### SEAMS

**Internal:** Stitched together with an elastic tape for security.

**External:** Vulcanised with a 25 mm rubber tape.

Vulcanisation is a chemical bonding process, ensuring watertight seams.

### REINFORCEMENTS

Additional layers of anti-slip textured rubber are applied to areas at risk of wear. The shoulders and zipper are reinforced. The trouser rear reinforcement extends around the thigh and across to the front of the legs, and down over the boots.


### COLOUR

Red with black reinforcements, or all black.



THE WORLDWIDE  
DIVING STANDARD

# VIKING™ PRO



Internal stitched seam

## ZIPPER

**Red suits:** Heavy Duty (HD) magnetic; 90 cm long.

**Black suits:** Heavy Duty (HD) non-magnetic; 90 cm long.

The zipper is gas and watertight, and is placed across the shoulders.

## VALVES

Standard configuration, mounted on rubber backing discs:

- Push protected inlet valve, positioned centrally on the chest
- Hose: 80 cm long; CEJN fitting
- VIKING™ X2 exhaust valve, placed on the upper left arm

## NECK SEAL

Fitted with a Surveyor latex neck seal as standard.

**Option:** VIKING™ Quick Neck system, which allows for quick changing of broken seals.

## HOOD OPTIONS

May be fitted with a wide range of hood options as follows: Surveyor latex hood + thermal inner hood; Nautic neoprene hood with smooth face seal; Smoothskin hood; Turbo rubber hood; Magnum rubber hood.

## CUFFS

Latex PRO cuffs are the standard fitment.

**Options:** A rubber cuff ring system or the VIKING™ Bayonet Ring System. Both systems make the fitment of rubber gloves possible.

## FOOTWEAR

The standard boot is an extension of the leg, with a heavy duty flexible rubber outsole stitched and taped to the end.

The outsole features a non-slip surface for grip. The heel has a fin strap retainer. Alternative options are available.

## SIZE RANGE

- Regular: 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL, 05/XXXL
- Wide: 01/MED, 02/LGE, 03/EXL, 04/XXL
- Double Wide: 01/MED, 02/LGE, 03/EXL, 04/XXL

See the VIKING™ size chart for detailed size measurements along with boot sizing.

## INCLUDED WITH EACH DELIVERY

Each suit comes supplied with suspenders, carry bag, user manual, repair kit and zip care materials.

## CERTIFICATION & APPROVALS

- EN 14225-2:2005
- BIO micro-organism approval

**Ansell Protective Solutions AB**  
Johan Kocksgatan 10, SE-231 81 Trelleborg, Sweden  
Tel: +46 (0)10 205 1800, Fax: +46 (0)10 205 1840  
<http://protective.ansell.com> | [order.protective@ansell.com](mailto:order.protective@ansell.com)

® & ™ are trademarks owned by Ansell Limited or one of its affiliates.  
© 2017 Ansell Limited. All Rights Reserved.

**Ansell**