

## VIKING™ VSN

### AREAS OF USE

Sports/technical, military, police

### MATERIAL

- Inner & outer: Armatex knitted nylon
- Mid-ply: NR/EPDM
- Total material weight: 1100 g/m<sup>2</sup> ± 100 g/m<sup>2</sup>
- Unique, flexible and stretchy material

### SEAMS

External stitched and taped. Internal "Vulca Seam".

### COLOUR

Black

### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

### REINFORCEMENTS

Soft, flexible and hard-wearing knee pads are fitted as standard.

### ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Rear entry
- Front entry suits with zip flap and adjustable torso, available to special order only

### VALVES

- Push protected inlet valve
- Low profile exhaust valve
- Standard hose

### BOOTS

Neoprene lined rubber boots with fin keeper

### FEATURES/ACCESSORIES

- Latex or neoprene hood - optional
- VIKING Quick Neck collar system - optional
- Rubber cuff rings/Bayonet glove ring - optional
- Relief zip - optional
- Cargo or Tech pockets - optional
- PVC non safety boots - optional
- Removable suspenders fitted as standard
- Supplied with nylon carry bag and repair kit

### CERTIFICATION

EN 14225-2:2005



VIKING™ VSN

## VIKING™ VTS

### AREAS OF USE

Sports/technical, military, police

### MATERIAL

- 1) Cordura/Butyl/Polyester, 450 g/m<sup>2</sup>.  
Light and strong with high puncture resistance. Textured finish.
- 2) Polyester/Butyl/Polyester, 400 g/m<sup>2</sup>.  
Soft, warm feel. High abrasion and puncture resistance.

### SEAMS

External stitched. Internal "Vulca Seam".

### COLOUR

Black

### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

### REINFORCEMENTS

Soft, flexible and hard-wearing knee pads are fitted as standard.

### ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Rear entry
- Front entry suits with zip flap and adjustable torso, available to special order only

### VALVES

- Push protected inlet valve
- Low profile exhaust valve
- Standard hose

### BOOTS

Neoprene lined rubber boots with fin keeper

### FEATURES/ACCESSORIES

- Latex or neoprene hood - optional
- VIKING Quick Neck collar system - optional
- Rubber cuff rings/Bayonet glove ring - optional
- Relief zip - optional
- Cargo or Tech pockets - optional
- PVC non safety boots - optional
- Removable suspenders fitted as standard
- Supplied with nylon carry bag and repair kit

### CERTIFICATION

EN 14225-2:2005



VIKING™ VTS



## TRILAMINATE DRY SUITS



VIKING™ SRS

### VIKING™ SRS (SURFACE RESCUE SUIT)

#### AREAS OF USE

Fire & Rescue, environmental work, coastguard

#### MATERIAL

Cordura/Butyl/Polyester, 450 g/m<sup>2</sup>.

Light and strong with high puncture resistance. Textured finish.

#### SEAMS

External stitched. Internal "Vulca Seam".

#### COLOUR

Black lower body with yellow or red top

#### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

#### REINFORCEMENTS

Soft, flexible and hard-wearing knee pads are fitted as standard.

#### ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Front entry adjustable torso

#### VALVES

None

#### BOOTS

Neoprene lined rubber boots with fin keeper

#### FEATURES/ACCESSORIES

- Latex or neoprene hood - optional
- VIKING Quick Neck collar system - optional
- Rubber cuff rings/Bayonet glove ring - optional
- Relief zip - optional
- Cargo or Tech pockets - optional
- PVC non safety boots - optional
- Nitrile safety boots - optional
- Latex socks - optional
- Removable suspenders fitted as standard
- SOLAS reflectors fitted to front and back wrists, rear of legs and upper arms - standard
- Supplied with nylon carry bag and repair kit

#### CERTIFICATION

89/686/EEC using applicable parts of EN 15027-1



VIKING™ WRS

### VIKING™ WRS (WATER RESCUE SUIT)

#### AREAS OF USE

Fire & Rescue, environmental work, coastguard

#### MATERIAL

Nylon/Butyl/Nylon, 255 g/m<sup>2</sup>.

Lightweight with high abrasion and puncture resistance.

#### SEAMS

External stitched. Internal "Vulca Seam".

#### COLOUR

Black lower body with black or yellow top

#### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

#### REINFORCEMENTS

Additional reinforcements are fitted as standard to the knees and elbows.

#### ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Front entry, non adjustable torso only

#### VALVES

None

#### BOOTS

Neoprene lined rubber boots with fin keeper

#### FEATURES/ACCESSORIES

- Latex or neoprene hood - optional
- VIKING Quick Neck collar system - optional
- Rubber cuff rings/Bayonet glove ring - optional
- Relief zip - optional
- Cargo or Tech pockets - optional
- PVC non safety boots - optional
- Nitrile safety boots - optional
- Latex socks - optional
- Removable suspenders fitted as standard
- High visibility reflectors fitted as standard to the zip flap, wrists, upper arms and rear of legs
- Supplied with nylon carry bag and repair kit

#### CERTIFICATION

89/686/EEC using applicable parts of EN 15027-1



VIKING™ HWS MK 2

### VIKING™ HWS MK 2 (HOT WATER SUIT)

#### AREAS OF USE

Commercial, navy

#### MATERIAL

- Suit construction: 5 mm neoprene
- Suit exterior: RO-TEX™ nylon with PU top coating
- Underarm panels and pockets: 3 mm material

#### SEAMS

Double glued and stitched. The seam across the lower torso additionally coated.

#### COLOUR

Black with contrasting grey stitching

#### SIZE RANGE

SML, MED, LGE, EXL, XXL, TSM, MET, LGT, EXT

#### REINFORCEMENTS

PU protection is added to elbows and knees.

#### ZIPPER

Non corroding nylon center zip

#### VALVE

- Thigh mounted "click" function variable flow valve. HIGH, MED & LOW flow and dump
- Controls flow of water through internal rubber tubing

#### BOOTS

Optional 5 mm neoprene boots (not fitted)

#### FEATURES/ACCESSORIES

- Flexible material and pattern layout
- RO-TEX™ nylon exterior with high abrasion resistance
- PU top coating for ease of cleaning
- Glued and stitched seams, with front seams coated for protection
- PU knee and elbow protection
- New "click" function valve with 3 flow settings and a dump mode
- 3 mm underarm panels for freedom of movement
- Optional accessories: 5 mm neoprene gauntlet gloves and/or boots

#### CERTIFICATION

EN 14225-3