



## DRYSUITS FOR CONTAMINATED WATER DIVING



VIKING™ PRO



PRO BLACK

### VIKING™ PRO

#### AREAS OF USE

Fire & Rescue, military, sports/technical

#### MATERIAL

NR/EPDM with 2-way stretch polyester lining.  
Total material weight: 1,000 ± 100 g/m<sup>2</sup>.

#### SEAMS

Internal taped & stitched. External vulcanized.

#### COLOUR

Red with black reinforcements or all black.

#### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL, 05/XXXL
- 01/MED-05/XXXL Wide
- 01/MED-05/XXXL D Wide

#### REINFORCEMENTS

Shoulders and arms. Crotch, across the seat area and extending down to the front of the legs and down across the boots. Fin strap keeper on boots.

#### ZIPPER

- 90 cm HD zipper
- Non-mag version on black suits

#### VALVES

- Push protected inlet valve
- Viking X2 exhaust valve
- Standard hose

#### ACCESSORIES

- Range of hoods and neck seal options
- Rubber cuff ring or bayonet ring system
- Rubber pocket options
- Relief zip
- Nitrile safety boots, PVC wellies or neoprene boots
- Dry glove options including latex or rubber gloves
- Rubber or latex mittens

#### CERTIFICATION & APPROVALS

- EN 14225-2:2005
- BIO approval



VIKING™ PROTECH

### VIKING™ PROTECH

#### AREAS OF USE

Fire & Rescue, military, sports/technical

#### MATERIAL

NR/EPDM with 4-way stretch polyamide/elastane lining.

Total material weight: 1,250 ± 100 g/m<sup>2</sup>.

#### SEAMS

Internal taped & stitched. External vulcanized.

#### COLOUR

All black (military Combat version has black logos).

#### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL, 05/XXXL
- 01/MED-05/XXXL Wide
- 01/MED-05/XXXL D Wide

#### REINFORCEMENTS

Shoulders and arms. Crotch, across the seat area and extending down to the front of the legs and down to the front of the neoprene boots. Fin strap keeper on boots.

#### ZIPPER

- 90 cm medium duty non-mag zipper on rear entry suits
- 85 cm medium duty non-mag zipper on front entry versions \*

#### VALVES

- Push protected inlet valve
- Low profile exhaust valve
- Standard hose

#### ACCESSORIES

- Range of hoods and neck seal options
- Rubber cuff ring or bayonet ring system
- Rubber pocket options
- Relief zip
- Nitrile safety boots or PVC wellies
- Dry glove options including latex or rubber gloves
- Rubber or latex mittens

#### CERTIFICATION & APPROVALS

- EN 14225-2:2005
- BIO approval
- The PROTECH BE NAVY suit, fitted with HD zipper, also has HZ chemical approval

\* Front entry version available to special order only.



VIKING™ HD



HD BLACK

### VIKING™ HD

#### AREAS OF USE

Commercial, military

#### MATERIAL

NR/EPDM with 2-way stretch polyester lining.  
Total material weight: 1,550 ± 100 g/m<sup>2</sup>.

#### SEAMS

Internal taped & stitched. External vulcanized.

#### COLOUR

Red with black reinforcements or all black.

#### SIZE RANGE

- 01/MED, 02/LGE, 03/EXL, 04/XXL
- 01/MED Wide-04/XXL Wide

#### REINFORCEMENTS

Across shoulders and down the arms. Reinforced crotch. Above knees, down the legs and across the boots.

#### ZIPPER

- 90 cm HD zipper
- Non-mag version on black suits

#### VALVES

- Push protected inlet valve
- Viking X2 exhaust valve
- Standard hose

#### ACCESSORIES

- Range of hoods, neck seals and helmet yokes
- Rubber cuff ring or bayonet ring system
- Rubber pocket options
- Relief zip
- Nitrile safety boots or PVC wellies
- Dry glove options including latex or rubber gloves
- Rubber or latex mittens

#### CERTIFICATION & APPROVALS

- EN 14225-2:2005
- HZ chemical approval
- BIO approval



## DRYSUITS FOR CONTAMINATED WATER DIVING



VIKING™ HDS

### VIKING™ HDS

#### AREAS OF USE

Fire & Rescue, police, hazmat, military, commercial

#### MATERIAL

NITECS NBR/EPDM blend on knitted black polyester stretch lining.

Total material weight: 1,050 ± 100 g/m<sup>2</sup>.

#### SEAMS

Internal taped & stitched. External vulcanized.

#### COLOUR

Black with black NITECS reinforcements.

#### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL, 05/XXXL
- 01/MED-05/XXXL Wide
- 01/MED-05/XXXL D Wide

#### REINFORCEMENTS

Shoulders and arms. Crotch, across the seat area and extending down to the front of the legs and down across the boots. Fin strap keeper on boots.

#### ZIPPER

- 90 cm HD zipper

#### VALVES

- Viking Hazmat inlet valve
- Viking X2 exhaust valve
- Standard hose

#### ACCESSORIES

- HDS Magnum hoods and yokes for contaminated water diving
- HDS rubber cuff ring system
- Rubber pocket options
- Relief zip
- Nitrile safety boots or PVC wellies
- Dry glove options including latex or rubber gloves
- Rubber or latex mittens

#### CERTIFICATION & APPROVALS

- EN 14225-2:2005
- HZ chemical approval
- BIO approval



VIKING™ DD

### VIKING™ DD

#### AREAS OF USE

Commercial helmet diving

#### MATERIAL

NR/EPDM with 2-way stretch polyester lining. Total material weight: 1,550 ± 100 g/m<sup>2</sup>.

#### SEAMS

Internal taped & stitched. External vulcanized.

#### COLOUR

Red with black reinforcements or all black.

#### SIZE RANGE

- 01/MED, 02/LGE, 03/EXL, 04/XXL

#### REINFORCEMENTS

Additional layers of rubber are added to the legs from above the knees and down to the boots, which have a soft sole.

#### ZIPPER

- None
- Neck entry through the collar

#### VALVES

None. All functions are handled through the helmet.

#### ACCESSORIES

- Range of collars to fit the most popular classic helmets
- Rubber cuff ring system
- Rubber pocket options
- Relief zip
- Nitrile safety boots or PVC wellies
- Dry glove options including latex or rubber gloves
- Rubber or latex mittens

#### CERTIFICATION & APPROVALS

- EN 14225-2:2005
- HZ chemical approval
- BIO approval



HAZTECH BLACK



VIKING™ HAZTECH

### VIKING™ HAZTECH

#### AREAS OF USE

Fire & Rescue, contaminated water diving, warm water/climate diving

#### MATERIAL

TPU (thermoplastic polyurethane), single coated onto a black knitted nylon fabric.

Total material weight: 480 g ± 40 g/m<sup>2</sup>.

#### SEAMS

High frequency welded. Taped on the inside for visual appearances.

#### COLOUR

Red with black reinforcements or all black.

#### SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

#### REINFORCEMENTS

A 1 mm PU film is welded onto shoulders and elbows. The knee area is similarly protected.

#### ZIPPER

- Red/black suit: 90 cm medium duty zipper made from a TPU coated fabric
- Black suit: 90 cm non-mag zipper
- High frequency welded to the suit

#### VALVES

- Push protected inlet valve
- Viking X2 exhaust valve
- Standard hose

#### ACCESSORIES

- Latex or neoprene hood, or HDS Magnum hoods and yokes for contaminated water diving
- VIKING Quick Neck collar system
- HDS rubber cuff ring or bayonet ring system
- PU bellows pockets
- Nitrile safety boots, PVC wellies or neoprene boots

#### CERTIFICATION & APPROVALS

- EN 14225-2:2005
- HZ chemical approval
- BIO approval