



TRILAMINATE DRY SUITS



VIKING™ VSN

VIKING™ VSN

AREAS OF USE

Sports/technical, military, police

MATERIAL

- Inner & outer: Armatex knitted nylon
- Mid-ply: NR/EPDM
- Total material weight: 1100 g/m² ± 100 g/m²
- Unique, flexible and stretchy material

SEAMS

External stitched & taped. Internal "Vulca Seam".

COLOUR

Black

SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

REINFORCEMENTS

Soft, flexible and hard-wearing knee pads are fitted as standard.

ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Rear entry
- Front entry suits with zip flap and adjustable torso, available to special order only

VALVES

- Push protected inlet valve
- Low profile exhaust valve
- Standard hose

BOOTS

Neoprene lined rubber boots with fin keeper

FEATURES/ACCESSORIES

- Latex or neoprene hood (optional)
- VIKING™ Quick Neck collar system (optional)
- Rubber cuff rings/Bayonet glove ring (optional)
- Relief zip (optional)
- Cargo or Tech pockets (optional)
- PVC non safety boots (optional)
- Removable suspenders fitted as standard
- Supplied with nylon carry bag and repair kit

CERTIFICATION

EN 14225-2:2005



VTS FRONT ENTRY



VIKING™ VTS

VIKING™ VTS

AREAS OF USE

Sports/technical, military, police

MATERIAL

- 1) **Nylon/Butyl/Nylon, 255 g/m²**
Lightweight with high abrasion and puncture resistance.
- 2) **Cordura/Butyl/Polyester, 450 g/m²**
Light and strong with high puncture resistance. Textured finish.
- 3) **Polyester/Butyl/Polyester, 400 g/m²**
Soft, warm feel. High abrasion and puncture resistance.

SEAMS

External stitched. Internal "Vulca Seam".

COLOUR

Black

SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

REINFORCEMENTS

Soft, flexible and hard-wearing knee pads are fitted as standard.

ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Rear entry
- Front entry suits with zip flap and adjustable torso, available to special order only

VALVES

- Push protected inlet valve
- Low profile exhaust valve
- Standard hose

BOOTS

Neoprene lined rubber boots with fin keeper

FEATURES/ACCESSORIES

- Latex or neoprene hood (optional)
- VIKING™ Quick Neck collar system (optional)
- Rubber cuff rings/Bayonet glove ring (optional)
- Relief zip (optional)
- Cargo or Tech pockets (optional)
- PVC non safety boots (optional)
- Removable suspenders fitted as standard
- Supplied with nylon carry bag and repair kit

CERTIFICATION

EN 14225-2:2005



VIKING™ HWS MK 2

VIKING™ HWS MK 2 (HOT WATER SUIT)

AREAS OF USE

Commercial, navy

MATERIAL

- Suit construction: 5 mm neoprene
- Suit exterior: RO-TEX™ nylon with PU top coating
- Underarm panels and pockets: 3 mm material

SEAMS

Double glued and stitched. The seam across the lower torso additionally coated.

COLOUR

Black with contrasting grey stitching

SIZE RANGE

SML, MED, LGE, EXL, XXL, TSM, MET, LGT, EXT

REINFORCEMENTS

PU protection is added to elbows and knees.

ZIPPER

Non corroding nylon center zip

VALVE

- Thigh mounted "click" function variable flow valve. HIGH, MED & LOW flow and dump
- Controls flow of water through internal rubber tubing

BOOTS

Optional 5 mm neoprene boots (not fitted)

FEATURES/ACCESSORIES

- Flexible material and pattern layout
- High abrasion resistance
- PU top coating for ease of cleaning
- Glued & stitched seams, with front seams coated for protection
- PU knee and elbow protection
- "Click" function valve with 3 flow settings and dump mode
- 3 mm underarm panels for freedom of movement
- Optional accessories: 5 mm neoprene gauntlet gloves and/or boots

CERTIFICATION

EN 14225-3



TRILAMINATE DRY SUITS



VIKING™ SRS

VIKING™ SRS (SURFACE RESCUE SUIT)

AREAS OF USE

Fire & Rescue, environmental work, coastguard

MATERIAL

Cordura/Butyl/Polyester, 450 g/m²
Light and strong with high puncture resistance. Textured finish.

SEAMS

External stitched. Internal "Vulca Seam".

COLOUR

Black lower body with yellow or red top

SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

REINFORCEMENTS

Soft, flexible and hard-wearing knee pads are fitted as standard.

ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Front entry adjustable torso

VALVES

None

BOOTS

Neoprene lined rubber boots with fin keeper

FEATURES/ACCESSORIES

- Latex or neoprene hood - optional
- VIKING™ Quick Neck collar system (optional)
- Rubber cuff rings/Bayonet glove ring (optional)
- Relief zip (optional)
- Cargo or Tech pockets (optional)
- PVC non safety boots (optional)
- Nitrile safety boots (optional)
- Latex socks (optional)
- Removable suspenders fitted as standard
- SOLAS reflectors fitted to front and back wrists, rear of legs and upper arms (standard)
- Supplied with nylon carry bag and repair kit

CERTIFICATION

89/686/EEC using applicable parts of EN 15027-1



VIKING™ WRS

VIKING™ WRS (WATER RESCUE SUIT)

AREAS OF USE

Fire & Rescue, environmental work, coastguard

MATERIAL

Nylon/Butyl/Nylon, 255 g/m²
Lightweight with high abrasion and puncture resistance.

SEAMS

External stitched. Internal "Vulca Seam".

COLOUR

Black lower body with black or yellow top

SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

REINFORCEMENTS

Additional reinforcements are fitted as standard to the knees and elbows.
Options: Padded knees and elbows for swift water operations. Buttock reinforcement panel.

ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Front entry, non adjustable torso only

VALVES

None

BOOTS

Neoprene lined rubber boots with fin keeper

FEATURES/ACCESSORIES

- Latex or neoprene hood - optional
- VIKING™ Quick Neck collar system (optional)
- Rubber cuff rings/Bayonet glove ring (optional)
- Relief zip (optional)
- Cargo or Tech pockets (optional)
- PVC non safety boots (optional)
- Nitrile safety boots (optional)
- Latex socks (optional)
- Removable suspenders fitted as standard
- High visibility reflectors fitted to zip flap, wrists, upper arms and rear of legs (standard)
- Supplied with nylon carry bag and repair kit

CERTIFICATION

89/686/EEC using applicable parts of EN 15027-1



VIKING™ WRS

VIKING™ WRS-D (COMBINED WATER RESCUE & DIVING SUIT)

AREAS OF USE

Fire & Rescue, law enforcement, military

MATERIAL

Nylon/Butyl/Nylon, 255 g/m²
Lightweight with high abrasion and puncture resistance.

SEAMS

External stitched. Internal "Vulca Seam".

COLOUR

Black lower body with black or yellow top

SIZE RANGE

- 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL
- 00/SML-04/XXL Wide
- 00/SML-04/XXL D Wide

REINFORCEMENTS

Additional reinforcements are fitted as standard to the knees and elbows.
Options: Padded knees and elbows for swift water operations. Buttock reinforcement panel.

ZIPPER

- MED duty non mag zipper
- Zip flap standard
- Front entry, non adjustable torso only

VALVES

- Push protected inlet valve
- Low profile exhaust valve
- Hose: CEJN fitting, 80 cm long

Valve blanking plugs may be fitted when the suit is being used purely as a surface rescue suit.

BOOTS

Neoprene lined rubber boots with fin keeper

FEATURES/ACCESSORIES

- Fitted with a bellows latex neck seal as standard
- Latex or neoprene hood - optional
- VIKING™ Quick Neck collar system (optional)
- Rubber cuff rings/Bayonet glove ring (optional)
- Relief zip (optional)
- Cargo or Tech pockets (optional)
- PVC non safety boots (optional)
- Nitrile safety boots (optional)
- Latex socks (optional)
- Removable suspenders fitted as standard
- High visibility reflectors fitted to zip flap, wrists, upper arms and rear of legs (standard)
- Supplied with nylon carry bag and repair kit

CERTIFICATION

EN 14225-2:2005