



INDUCER

Description

- The inducer is used for adding cleaning agents to your decontamination system in an accurate dosing.
- Inducers do not need any external power source. The flow in your system provides all the power needed.



1. Motor Piston
2. Clear water
3. Dosing piston
4. Adjustment (%) ratio
5. Concentrated additive to be dosed
6. Solution water + % Additive



Technical Specifications

Type:	Inducer in box
l x w x h:	60 x 40 x 23 cm.
Weight:	4,5 kg

Features

- Accurate dosing, regardless of flow and pressure
- Adjustable percentage of additive; standard 0.2%-2.0%
- Min. flow 10l/h, max. flow 2500l/h
- Operating pressure min 0.3, max 6 bar
- Built in filter 300 micron/50 mesh
- No external power source needed