

THE WORLDWIDE
DIVING STANDARD

VIKING™ PROTECH II



VIKING™ PROTECH II with Surveyor latex hood.

Flexible dry suit designed for maximum comfort in a wide range of applications, particularly suited to military use. Rear entry design. Vulcanised seams allow for peace of mind when diving under all situations.

- Internal stitched and taped seams
- External vulcanised seams
- Easy to clean exterior when contaminated
- Easy to repair in the field to minimise downtime
- Extremely flexible and comfortable

DESIGN

Rear entry.

SUIT MATERIAL

Blend of natural and synthetic rubbers (NR/EPDM), on a stretch polyamide/elastane lining.

Total material weight: 1250 g/m² ± 100 g/m².

SEAMS

Internal: Stitched together with an elastic tape for security.

External: Vulcanised with a 25 mm rubber tape.

Vulcanisation is a chemical bonding process, ensuring watertight seams.

REINFORCEMENTS

Additional layers of anti-slip textured rubber are applied to areas at risk of wear. The shoulders, zipper and waistband are reinforced. The trouser rear reinforcement extends around the thigh and across to the front of the legs, and down to the boots.


COLOUR

All black. Military version has black logos.



THE WORLDWIDE
DIVING STANDARD

VIKING™ PROTECH II



Internal stitched seam

ZIPPER

Heavy Duty (HD) non-magnetic; 90 cm long.
The zipper is placed across the shoulders.

VALVES

Standard configuration, mounted on rubber backing discs:

- Push protected inlet valve, positioned centrally on the chest
- Hose: 80 cm long; CEJN fitting
- VIKING™ X2 exhaust valve with 2 mushroom valves for added security, positioned on the upper left arm

All valves are STD magnetic, unless non-magnetic versions are requested.

NECK SEAL

Fitted with a Surveyor latex neck seal as standard.

Option: VIKING™ Quick Neck system, which allows for quick changing of broken seals.

HOOD OPTIONS

May be fitted with a wide range of hood options as follows:
Surveyor latex hood + thermal inner hood, Nautic neoprene hood with smooth face seal or Smoothskin hood.

CUFFS

Latex PRO cuffs are the standard fitment.

Options: A rubber cuff ring system or the VIKING™ Bayonet Ring System. Both systems make the fitment of rubber gloves possible.

FOOTWEAR

Rubber coated 5 mm neoprene boots. The boots feature a non-slip outsole and a heel fin retainer. Options include extended legs with rubber outsole or Nitrile safety boots.

SIZE RANGE

- Regular: 00/SML, 01/MED, 02/LGE, 03/EXL, 04/XXL, 05/XXXL
- Wide: 01/MED, 02/LGE, 03/EXL, 04/XXL
- Double Wide: 01/MED, 02/LGE, 03/EXL, 04/XXL

See the VIKING™ size chart for detailed size measurements along with boot sizing.

INCLUDED WITH EACH DELIVERY

Each suit comes supplied with suspenders, carry bag, user manual, repair kit and zip care materials.

CERTIFICATION & APPROVALS

- EN 14225-2:2017
- BIO micro-organism approval
- HZ chemical approval

Ansell Protective Solutions AB
Arenagatan 8B
215 33 Malmö, Sweden
Tel: +46 10 205 1800
order.protective@ansell.com
http://protective.ansell.com

® & ™ are trademarks owned by Ansell Limited or one of its affiliates.
© 2019 Ansell Limited. All Rights Reserved.

Ansell